

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756670

Luminaire Tested: LD4D95BD010-EU4DR6570959027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6460.4 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756670

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756670

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	694975
5°	695546
10°	720041
15°	721233
20°	664011
25°	565769
30°	433119
35°	305993
40°	180626
45°	73319
50°	26585
55°	14801
60°	8500
65°	4679
70°	4920
75°	3799
80°	3964
85°	3385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 73319 cd/sqm



TEST NUMBER: P756670

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	612.5	9.5
10°-20°	1766.7	27.3
20°-30°	2119.8	32.8
30°-40°	1424.5	22.1
40°-50°	426.4	6.6
50°-60°	75.3	1.2
60°-70°	21.4	0.3
70°-80°	10.5	0.2
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4499.0	69.6
0°-40°	5923.5	91.7
0°-60°	6425.2	99.5
0°-90°	6460.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6460.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6361	
5°	6342	612
15°	6376	1767
25°	4693	2120
35°	2294	1425
45°	474	426
55°	78	75
65°	18	21
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P756670

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6360.7
2.5°	6387.8
5°	6341.7
7.5°	6437.6
10°	6490.0
12.5°	6477.3
15°	6376.1
17.5°	6128.4
20°	5710.8
22.5°	5219.1
25°	4693.0
27.5°	4099.2
30°	3433.0
32.5°	2829.2
35°	2294.1
37.5°	1765.3
40°	1266.4
42.5°	827.1
45°	474.5
47.5°	251.3
50°	156.4
52.5°	108.5
55°	77.7
57.5°	56.0
60°	38.9
62.5°	25.3
65°	18.1
67.5°	16.3
70°	15.4
72.5°	11.8
75°	9.0
77.5°	8.1
80°	6.3
82.5°	4.5
85°	2.7
87.5°	1.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)