

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756317

Luminaire Tested: LD4D95BD010-EU4DR4070959040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9721.3 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756317

CATALOG NUMBER: LD4D95BD010-EU4DR4070959040-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P756317

CATALOG NUMBER: LD4D95BD010-EU4DR4070959040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2472986
5°	2460968
10°	2326144
15°	1977523
20°	1347823
25°	562369
30°	176831
35°	82190
40°	45456
45°	20844
50°	10114
55°	5543
60°	2884
65°	1034
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20844 cd/sqm



TEST NUMBER: P756317

CATALOG NUMBER: LD4D95BD010-EU4DR4070959040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2095.1	21.6
10°-20°	4693.7	48.3
20°-30°	2349.5	24.2
30°-40°	430.7	4.4
40°-50°	118.8	1.2
50°-60°	27.9	0.3
60°-70°	5.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9138.4	94.0
0°-40°	9569.1	98.4
0°-60°	9715.8	99.9
0°-90°	9721.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9721.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22634	
5°	22438	###
15°	17482	4694
25°	4665	2350
35°	616	431
45°	135	119
55°	29	28
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756317

CATALOG NUMBER: LD4D95BD010-EU4DR4070959040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	22633.8
2.5°	22600.7
5°	22438.1
7.5°	21919.8
10°	20966.4
12.5°	19480.3
15°	17482.4
17.5°	14884.2
20°	11591.9
22.5°	7902.9
25°	4664.8
27.5°	2465.9
30°	1401.6
32.5°	905.7
35°	616.2
37.5°	440.3
40°	318.7
42.5°	218.2
45°	134.9
47.5°	85.9
50°	59.5
52.5°	42.3
55°	29.1
57.5°	18.5
60°	13.2
62.5°	7.9
65°	4.0
67.5°	2.6
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)