

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756673

Luminaire Tested: LD4D95BD010-EU4DR6570959027-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P756673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8276.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756673

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756673

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	438870
5°	437762
10°	437385
15°	423902
20°	385915
25°	336295
30°	279703
35°	221623
40°	159961
45°	101056
50°	52672
55°	28002
60°	14706
65°	8084
70°	3398
75°	3746
80°	2590
85°	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 101056 cd/sqm



TEST NUMBER: P756673

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	710.6	8.6
10°-20°	1946.0	23.5
20°-30°	2378.6	28.7
30°-40°	1929.9	23.3
40°-50°	961.7	11.6
50°-60°	268.2	3.2
60°-70°	60.9	0.7
70°-80°	15.9	0.2
80°-90°	4.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5035.2	60.8
0°-40°	6965.1	84.2
0°-60°	8195.1	99.0
0°-90°	8276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8276.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7514	
5°	7467	711
15°	7011	1946
25°	5219	2379
35°	3108	1930
45°	1224	962
55°	275	268
65°	58	61
75°	17	16
85°	3	4
90°	0	



TEST NUMBER: P756673

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7514.4
2.5°	7508.8
5°	7466.9
7.5°	7442.6
10°	7375.2
12.5°	7238.3
15°	7010.8
17.5°	6655.3
20°	6209.2
22.5°	5727.7
25°	5218.6
27.5°	4674.3
30°	4147.5
32.5°	3627.4
35°	3108.4
37.5°	2590.6
40°	2098.1
42.5°	1636.5
45°	1223.5
47.5°	852.5
50°	579.7
52.5°	399.7
55°	275.0
57.5°	185.5
60°	125.9
62.5°	87.2
65°	58.5
67.5°	29.8
70°	19.9
72.5°	18.8
75°	16.6
77.5°	11.0
80°	7.7
82.5°	5.5
85°	3.3
87.5°	2.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)