

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756752

Luminaire Tested: LD4D95BD010-EU4DR7070959027-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR7070959027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8621.9 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756752

CATALOG NUMBER: LD4D95BD010-EU4DR7070959027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756752

CATALOG NUMBER: LD4D95BD010-EU4DR7070959027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	743530
5°	741676
10°	740067
15°	739863
20°	732635
25°	688217
30°	613545
35°	489181
40°	324825
45°	194198
50°	100679
55°	52918
60°	18727
65°	310
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 194198 cd/sqm

TEST NUMBER: P756752

CATALOG NUMBER: LD4D95BD010-EU4DR7070959027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	643.1	7.5
10°-20°	1844.4	21.4
20°-30°	2601.9	30.2
30°-40°	2246.1	26.1
40°-50°	1005.9	11.7
50°-60°	263.4	3.1
60°-70°	17.1	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5089.4	59.0
0°-40°	7335.5	85.1
0°-60°	8604.8	99.8
0°-90°	8621.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8621.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6805	
5°	6762	643
15°	6541	1844
25°	5709	2602
35°	3668	2246
45°	1257	1006
55°	278	263
65°	1	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756752

CATALOG NUMBER: LD4D95BD010-EU4DR7070959027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6805.1
2.5°	6797.8
5°	6762.3
7.5°	6732.9
10°	6670.5
12.5°	6614.2
15°	6540.8
17.5°	6456.4
20°	6301.0
22.5°	6045.2
25°	5708.7
27.5°	5318.3
30°	4863.1
32.5°	4306.3
35°	3667.5
37.5°	2962.6
40°	2277.4
42.5°	1730.3
45°	1256.8
47.5°	866.4
50°	592.3
52.5°	408.7
55°	277.8
57.5°	167.7
60°	85.7
62.5°	26.9
65°	1.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)