

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756060

Luminaire Tested: LD4D95BD010-EU4DR2570959030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR2570959030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7751.7 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756060

CATALOG NUMBER: LD4D95BD010-EU4DR2570959030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P756060

CATALOG NUMBER: LD4D95BD010-EU4DR2570959030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3212332
5°	2991887
10°	2134196
15°	1256957
20°	782098
25°	429215
30°	196298
35°	74334
40°	33661
45°	20242
50°	8397
55°	5410
60°	3780
65°	2559
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20242 cd/sqm



TEST NUMBER: P756060

CATALOG NUMBER: LD4D95BD010-EU4DR2570959030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2344.4	30.2
10°-20°	3175.3	41.0
20°-30°	1680.3	21.7
30°-40°	414.8	5.4
40°-50°	101.2	1.3
50°-60°	26.6	0.3
60°-70°	8.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7200.0	92.9
0°-40°	7614.8	98.2
0°-60°	7742.6	99.9
0°-90°	7751.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7751.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29401	
5°	27279	###
15°	11112	3175
25°	3560	1680
35°	557	415
45°	131	101
55°	28	27
65°	10	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756060

CATALOG NUMBER: LD4D95BD010-EU4DR2570959030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	29400.6
2.5°	28917.4
5°	27278.8
7.5°	23986.6
10°	19236.3
12.5°	14541.5
15°	11112.2
17.5°	8660.4
20°	6726.4
22.5°	5044.5
25°	3560.3
27.5°	2387.5
30°	1555.9
32.5°	946.6
35°	557.3
37.5°	341.1
40°	236.0
42.5°	180.4
45°	131.0
47.5°	79.1
50°	49.4
52.5°	35.8
55°	28.4
57.5°	22.2
60°	17.3
62.5°	13.6
65°	9.9
67.5°	3.7
70°	1.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)