

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756477

Luminaire Tested: LD4D95BD010-EU4DR5070959040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10168.5 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756477

CATALOG NUMBER: LD4D95BD010-EU4DR5070959040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P756477

CATALOG NUMBER: LD4D95BD010-EU4DR5070959040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1790128
5°	1771367
10°	1742189
15°	1586405
20°	1320069
25°	937057
30°	495986
35°	202115
40°	75066
45°	34365
50°	14091
55°	7372
60°	3627
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34365 cd/sqm



TEST NUMBER: P756477

CATALOG NUMBER: LD4D95BD010-EU4DR5070959040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1526.5	15.0
10°-20°	3857.9	37.9
20°-30°	3465.4	34.1
30°-40°	1085.0	10.7
40°-50°	190.0	1.9
50°-60°	37.9	0.4
60°-70°	5.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8849.9	87.0
0°-40°	9934.9	97.7
0°-60°	10162.8	99.9
0°-90°	10168.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10168.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16384	
5°	16151	###
15°	14025	3858
25°	7773	3465
35°	1515	1085
45°	222	190
55°	39	38
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756477

CATALOG NUMBER: LD4D95BD010-EU4DR5070959040-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	16384.0
2.5°	16302.5
5°	16150.6
7.5°	15918.5
10°	15703.0
12.5°	15012.3
15°	14024.7
17.5°	12770.4
20°	11353.2
22.5°	9713.5
25°	7772.8
27.5°	5714.6
30°	3931.3
32.5°	2559.6
35°	1515.3
37.5°	870.2
40°	526.3
42.5°	342.6
45°	222.4
47.5°	135.4
50°	82.9
52.5°	56.6
55°	38.7
57.5°	26.2
60°	16.6
62.5°	9.7
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)