

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756213

Luminaire Tested: LD4D95BD010-EU4DR3570959030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8408.8 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756213

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P756213

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2527933
5°	2468536
10°	2224806
15°	1726803
20°	979413
25°	381041
30°	142148
35°	77922
40°	50933
45°	30996
50°	19735
55°	13944
60°	10205
65°	5533
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30996 cd/sqm



TEST NUMBER: P756213

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2070.0	24.6
10°-20°	4041.5	48.1
20°-30°	1648.3	19.6
30°-40°	394.4	4.7
40°-50°	164.4	2.0
50°-60°	68.0	0.8
60°-70°	21.3	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7759.8	92.3
0°-40°	8154.2	97.0
0°-60°	8386.6	99.7
0°-90°	8408.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8408.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23137	
5°	22507	###
15°	15266	4042
25°	3161	1648
35°	584	394
45°	201	164
55°	73	68
65°	21	21
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P756213

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	23136.7
2.5°	22997.9
5°	22507.1
7.5°	21527.9
10°	20053.0
12.5°	17976.1
15°	15265.9
17.5°	11951.3
20°	8423.4
22.5°	5371.3
25°	3160.7
27.5°	1786.6
30°	1126.7
32.5°	791.1
35°	584.2
37.5°	451.7
40°	357.1
42.5°	275.1
45°	200.6
47.5°	150.1
50°	116.1
52.5°	92.1
55°	73.2
57.5°	59.3
60°	46.7
62.5°	34.1
65°	21.4
67.5°	7.6
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)