

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756373

Luminaire Tested: LD4D95BD010-EU4DR4570959030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4570959030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9491.2 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756373

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P756373

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1832947
5°	1780756
10°	1703702
15°	1559246
20°	1237027
25°	772293
30°	425663
35°	191137
40°	75280
45°	35477
50°	16828
55°	8801
60°	4327
65°	1034
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35477 cd/sqm

TEST NUMBER: P756373

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1525.5	16.1
10°-20°	3754.6	39.6
20°-30°	2973.2	31.3
30°-40°	990.1	10.4
40°-50°	196.5	2.1
50°-60°	44.6	0.5
60°-70°	6.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8253.3	87.0
0°-40°	9243.5	97.4
0°-60°	9484.6	99.9
0°-90°	9491.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9491.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16776	
5°	16236	###
15°	13785	3755
25°	6406	2973
35°	1433	990
45°	230	197
55°	46	45
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756373

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	16775.9
2.5°	16666.4
5°	16236.2
7.5°	15881.3
10°	15356.1
12.5°	14656.8
15°	13784.6
17.5°	12473.1
20°	10639.0
22.5°	8453.9
25°	6406.1
27.5°	4690.8
30°	3373.9
32.5°	2294.6
35°	1433.0
37.5°	849.7
40°	527.8
42.5°	347.0
45°	229.6
47.5°	147.8
50°	99.0
52.5°	66.0
55°	46.2
57.5°	30.3
60°	19.8
62.5°	10.6
65°	4.0
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)