

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756252

Luminaire Tested: LD4D95BD010-EU4DR3570959050-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8958.2 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756252

CATALOG NUMBER: LD4D95BD010-EU4DR3570959050-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P756252

CATALOG NUMBER: LD4D95BD010-EU4DR3570959050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2693092
5°	2629807
10°	2370156
15°	1839624
20°	1043409
25°	405936
30°	151447
35°	83017
40°	54256
45°	33021
50°	21026
55°	14858
60°	10861
65°	5920
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33021 cd/sqm

TEST NUMBER: P756252

CATALOG NUMBER: LD4D95BD010-EU4DR3570959050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2205.2	24.6
10°-20°	4305.6	48.1
20°-30°	1756.0	19.6
30°-40°	420.2	4.7
40°-50°	175.1	2.0
50°-60°	72.5	0.8
60°-70°	22.7	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8266.8	92.3
0°-40°	8687.0	97.0
0°-60°	8934.6	99.7
0°-90°	8958.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8958.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24648	
5°	23978	###
15°	16263	4306
25°	3367	1756
35°	622	420
45°	214	175
55°	78	72
65°	23	23
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P756252

CATALOG NUMBER: LD4D95BD010-EU4DR3570959050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	24648.3
2.5°	24500.4
5°	23977.5
7.5°	22934.4
10°	21363.1
12.5°	19150.6
15°	16263.3
17.5°	12732.1
20°	8973.8
22.5°	5722.2
25°	3367.2
27.5°	1903.4
30°	1200.4
32.5°	842.8
35°	622.4
37.5°	481.2
40°	380.4
42.5°	293.0
45°	213.7
47.5°	160.0
50°	123.7
52.5°	98.1
55°	78.0
57.5°	63.2
60°	49.7
62.5°	36.3
65°	22.9
67.5°	8.1
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)