

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756449

Luminaire Tested: LD4D95BD010-EU4DR5070959030-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8685.9 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756449

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P756449

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1529126
5°	1513097
10°	1488178
15°	1355107
20°	1127603
25°	800431
30°	423669
35°	172651
40°	64126
45°	29358
50°	12035
55°	6286
60°	3103
65°	905
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29358 cd/sqm



TEST NUMBER: P756449

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1304.0	15.0
10°-20°	3295.4	37.9
20°-30°	2960.2	34.1
30°-40°	926.8	10.7
40°-50°	162.3	1.9
50°-60°	32.3	0.4
60°-70°	4.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7559.6	87.0
0°-40°	8486.4	97.7
0°-60°	8681.1	99.9
0°-90°	8685.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8685.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13995	
5°	13796	###
15°	11980	3295
25°	6640	2960
35°	1294	927
45°	190	162
55°	33	32
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756449

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13995.2
2.5°	13925.6
5°	13795.8
7.5°	13597.6
10°	13413.5
12.5°	12823.6
15°	11979.9
17.5°	10908.5
20°	9697.9
22.5°	8297.3
25°	6639.5
27.5°	4881.4
30°	3358.1
32.5°	2186.4
35°	1294.4
37.5°	743.4
40°	449.6
42.5°	292.6
45°	190.0
47.5°	115.6
50°	70.8
52.5°	48.4
55°	33.0
57.5°	22.4
60°	14.2
62.5°	8.3
65°	3.5
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)