

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756452

Luminaire Tested: LD4D95BD010-EU4DR5070959030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10093.8 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756452

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756452

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1776962
5°	1758338
10°	1729386
15°	1574743
20°	1310360
25°	930161
30°	492340
35°	200634
40°	74510
45°	34118
50°	13989
55°	7315
60°	3606
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34118 cd/sqm



TEST NUMBER: P756452

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1515.3	15.0
10°-20°	3829.6	37.9
20°-30°	3440.0	34.1
30°-40°	1077.0	10.7
40°-50°	188.6	1.9
50°-60°	37.6	0.4
60°-70°	5.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8784.8	87.0
0°-40°	9861.9	97.7
0°-60°	10088.1	99.9
0°-90°	10093.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10093.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16264	
5°	16032	###
15°	13922	3830
25°	7716	3440
35°	1504	1077
45°	221	189
55°	38	38
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756452

CATALOG NUMBER: LD4D95BD010-EU4DR5070959030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	16263.5
2.5°	16182.6
5°	16031.8
7.5°	15801.5
10°	15587.6
12.5°	14902.0
15°	13921.6
17.5°	12676.5
20°	11269.7
22.5°	9642.1
25°	7715.6
27.5°	5672.6
30°	3902.4
32.5°	2540.8
35°	1504.2
37.5°	863.8
40°	522.4
42.5°	340.1
45°	220.8
47.5°	134.4
50°	82.3
52.5°	56.2
55°	38.4
57.5°	26.1
60°	16.5
62.5°	9.6
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)