

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756529

Luminaire Tested: LD4D95BD010-EU4DR5570959030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9476.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756529

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P756529

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1160983
5°	1114878
10°	1110672
15°	1078767
20°	967262
25°	799394
30°	603844
35°	437829
40°	280196
45°	127972
50°	41849
55°	18058
60°	7779
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 127972 cd/sqm



TEST NUMBER: P756529

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	967.3	10.2
10°-20°	2639.8	27.9
20°-30°	3008.3	31.7
30°-40°	2047.9	21.6
40°-50°	705.7	7.4
50°-60°	97.6	1.0
60°-70°	9.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6615.3	69.8
0°-40°	8663.3	91.4
0°-60°	9466.5	99.9
0°-90°	9476.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9476.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10626	
5°	10165	967
15°	9537	2640
25°	6631	3008
35°	3282	2048
45°	828	706
55°	95	98
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756529

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	10625.8
2.5°	10382.2
5°	10165.0
7.5°	10058.3
10°	10010.9
12.5°	9852.9
15°	9536.9
17.5°	9035.2
20°	8318.9
22.5°	7492.0
25°	6630.9
27.5°	5734.2
30°	4786.2
32.5°	3983.0
35°	3282.5
37.5°	2616.3
40°	1964.5
42.5°	1361.5
45°	828.2
47.5°	446.4
50°	246.2
52.5°	146.2
55°	94.8
57.5°	60.6
60°	35.6
62.5°	15.8
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)