

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756486

Luminaire Tested: LD4D95BD010-EU4DR5070959050-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9729.1 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756486

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P756486

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1712772
5°	1694812
10°	1666901
15°	1517846
20°	1263026
25°	896562
30°	474551
35°	193378
40°	71814
45°	32881
50°	13479
55°	7048
60°	3474
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32881 cd/sqm



TEST NUMBER: P756486

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1460.6	15.0
10°-20°	3691.2	37.9
20°-30°	3315.7	34.1
30°-40°	1038.1	10.7
40°-50°	181.8	1.9
50°-60°	36.2	0.4
60°-70°	5.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8467.5	87.0
0°-40°	9505.6	97.7
0°-60°	9723.6	99.9
0°-90°	9729.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9729.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15676	
5°	15453	###
15°	13419	3691
25°	7437	3316
35°	1450	1038
45°	213	182
55°	37	36
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756486

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	15676.0
2.5°	15598.0
5°	15452.6
7.5°	15230.6
10°	15024.4
12.5°	14363.6
15°	13418.6
17.5°	12218.6
20°	10862.6
22.5°	9293.8
25°	7436.9
27.5°	5467.6
30°	3761.4
32.5°	2449.0
35°	1449.8
37.5°	832.6
40°	503.5
42.5°	327.8
45°	212.8
47.5°	129.5
50°	79.3
52.5°	54.2
55°	37.0
57.5°	25.1
60°	15.9
62.5°	9.3
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)