

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756487

Luminaire Tested: LD4D95BD010-EU4DR5070959050-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10215.6 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756487

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756487

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76		
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65		
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62		
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1798410
5°	1779560
10°	1750244
15°	1593746
20°	1326173
25°	941385
30°	498283
35°	203049
40°	75408
45°	34519
50°	14159
55°	7410
60°	3649
65°	1086
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34519 cd/sqm

TEST NUMBER: P756487

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1533.6	15.0
10°-20°	3875.8	37.9
20°-30°	3481.5	34.1
30°-40°	1090.0	10.7
40°-50°	190.9	1.9
50°-60°	38.1	0.4
60°-70°	5.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8890.8	87.0
0°-40°	9980.9	97.7
0°-60°	10209.8	99.9
0°-90°	10215.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10215.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16460	
5°	16225	###
15°	14090	3876
25°	7809	3481
35°	1522	1090
45°	223	191
55°	39	38
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756487

CATALOG NUMBER: LD4D95BD010-EU4DR5070959050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	16459.8
2.5°	16377.9
5°	16225.3
7.5°	15992.1
10°	15775.6
12.5°	15081.8
15°	14089.6
17.5°	12829.5
20°	11405.7
22.5°	9758.5
25°	7808.7
27.5°	5741.0
30°	3949.5
32.5°	2571.5
35°	1522.3
37.5°	874.3
40°	528.7
42.5°	344.2
45°	223.4
47.5°	136.0
50°	83.3
52.5°	56.9
55°	38.9
57.5°	26.4
60°	16.7
62.5°	9.7
65°	4.2
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)