

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756225

Luminaire Tested: LD4D95BD010-EU4DR3570959035-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7355.1 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756225

CATALOG NUMBER: LD4D95BD010-EU4DR3570959035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P756225

CATALOG NUMBER: LD4D95BD010-EU4DR3570959035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96			
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88			
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84			
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75			
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70			
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2211165
5°	2159211
10°	1946020
15°	1510425
20°	856687
25°	333289
30°	124347
35°	68159
40°	44543
45°	27118
50°	17253
55°	12191
60°	8916
65°	4860
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27118 cd/sqm



TEST NUMBER: P756225

CATALOG NUMBER: LD4D95BD010-EU4DR3570959035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1810.6	24.6
10°-20°	3535.1	48.1
20°-30°	1441.7	19.6
30°-40°	345.0	4.7
40°-50°	143.8	2.0
50°-60°	59.5	0.8
60°-70°	18.6	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6787.4	92.3
0°-40°	7132.5	97.0
0°-60°	7335.8	99.7
0°-90°	7355.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7355.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20238	
5°	19687	###
15°	13353	3535
25°	2765	1442
35°	511	345
45°	176	144
55°	64	60
65°	19	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756225

CATALOG NUMBER: LD4D95BD010-EU4DR3570959035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	20237.5
2.5°	20116.1
5°	19686.8
7.5°	18830.4
10°	17540.2
12.5°	15723.6
15°	13353.0
17.5°	10453.7
20°	7367.9
22.5°	4698.2
25°	2764.6
27.5°	1562.8
30°	985.6
32.5°	692.0
35°	511.0
37.5°	395.1
40°	312.3
42.5°	240.6
45°	175.5
47.5°	131.3
50°	101.5
52.5°	80.6
55°	64.0
57.5°	51.9
60°	40.8
62.5°	29.8
65°	18.8
67.5°	6.6
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)