

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756539

Luminaire Tested: LD4D95BD010-EU4DR5570959035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9551.8 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756539

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756539

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1170281
5°	1123795
10°	1119570
15°	1087409
20°	975006
25°	805796
30°	608676
35°	441337
40°	282450
45°	128992
50°	42189
55°	18211
60°	7823
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 128992 cd/sqm

TEST NUMBER: P756539

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	975.0	10.2
10°-20°	2660.9	27.9
20°-30°	3032.4	31.7
30°-40°	2064.3	21.6
40°-50°	711.3	7.4
50°-60°	98.3	1.0
60°-70°	9.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6668.3	69.8
0°-40°	8732.6	91.4
0°-60°	9542.3	99.9
0°-90°	9551.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9551.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10711	
5°	10246	975
15°	9613	2661
25°	6684	3032
35°	3309	2064
45°	835	711
55°	96	98
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756539

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10710.9
2.5°	10465.3
5°	10246.3
7.5°	10138.8
10°	10091.1
12.5°	9931.8
15°	9613.3
17.5°	9107.6
20°	8385.5
22.5°	7552.0
25°	6684.0
27.5°	5780.2
30°	4824.5
32.5°	4014.9
35°	3308.8
37.5°	2637.2
40°	1980.3
42.5°	1372.4
45°	834.8
47.5°	449.9
50°	248.2
52.5°	147.3
55°	95.6
57.5°	61.1
60°	35.8
62.5°	15.9
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)