

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756543

Luminaire Tested: LD4D95BD010-EU4DR5570959035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10054.6 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756543

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756543

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1231871
5°	1182944
10°	1178494
15°	1144634
20°	1026329
25°	848207
30°	640721
35°	464572
40°	297312
45°	135790
50°	44416
55°	19163
60°	8238
65°	1086
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 135790 cd/sqm

TEST NUMBER: P756543

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1026.3	10.2
10°-20°	2801.0	27.9
20°-30°	3192.0	31.7
30°-40°	2173.0	21.6
40°-50°	748.8	7.4
50°-60°	103.5	1.0
60°-70°	10.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7019.3	69.8
0°-40°	9192.3	91.4
0°-60°	10044.6	99.9
0°-90°	10054.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10054.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11275	
5°	10786	###
15°	10119	2801
25°	7036	3192
35°	3483	2173
45°	879	749
55°	101	104
65°	4	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756543

CATALOG NUMBER: LD4D95BD010-EU4DR5570959035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	11274.6
2.5°	11016.2
5°	10785.6
7.5°	10672.5
10°	10622.2
12.5°	10454.5
15°	10119.2
17.5°	9586.9
20°	8826.9
22.5°	7949.5
25°	7035.8
27.5°	6084.4
30°	5078.5
32.5°	4226.2
35°	3483.0
37.5°	2776.0
40°	2084.5
42.5°	1444.6
45°	878.8
47.5°	473.6
50°	261.3
52.5°	155.1
55°	100.6
57.5°	64.3
60°	37.7
62.5°	16.8
65°	4.2
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)