

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756693

Luminaire Tested: LD4D95BD010-EU4DR6570959035-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6570959035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5806.7 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756693

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P756693

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	624655
5°	625165
10°	647172
15°	648251
20°	596817
25°	508517
30°	389290
35°	275022
40°	162341
45°	65902
50°	23899
55°	13315
60°	7626
65°	4188
70°	4409
75°	3419
80°	3586
85°	3009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 65902 cd/sqm



TEST NUMBER: P756693

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	550.5	9.5
10°-20°	1588.0	27.3
20°-30°	1905.3	32.8
30°-40°	1280.4	22.1
40°-50°	383.3	6.6
50°-60°	67.7	1.2
60°-70°	19.2	0.3
70°-80°	9.4	0.2
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4043.7	69.6
0°-40°	5324.1	91.7
0°-60°	5775.0	99.5
0°-90°	5806.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5806.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5717	
5°	5700	551
15°	5731	1588
25°	4218	1905
35°	2062	1280
45°	426	383
55°	70	68
65°	16	19
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P756693

CATALOG NUMBER: LD4D95BD010-EU4DR6570959035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5717.1
2.5°	5741.4
5°	5700.0
7.5°	5786.1
10°	5833.2
12.5°	5821.9
15°	5730.9
17.5°	5508.3
20°	5132.9
22.5°	4691.0
25°	4218.1
27.5°	3684.4
30°	3085.6
32.5°	2542.9
35°	2061.9
37.5°	1586.7
40°	1138.2
42.5°	743.4
45°	426.5
47.5°	225.9
50°	140.6
52.5°	97.5
55°	69.9
57.5°	50.4
60°	34.9
62.5°	22.7
65°	16.2
67.5°	14.6
70°	13.8
72.5°	10.6
75°	8.1
77.5°	7.3
80°	5.7
82.5°	4.1
85°	2.4
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)