

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738963

Luminaire Tested: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P738963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 346.2 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P738963

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P738963

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215320
5°	194262
10°	109027
15°	55426
20°	23464
25°	10838
30°	5740
35°	3094
40°	1655
45°	973
50°	561
55°	305
60°	197
65°	129
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 973 cd/sqm



TEST NUMBER: P738963

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.3	40.5
10°-20°	138.2	39.9
20°-30°	45.1	13.0
30°-40°	15.4	4.4
40°-50°	5.2	1.5
50°-60°	1.6	0.4
60°-70°	0.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.6	93.5
0°-40°	339.0	97.9
0°-60°	345.7	99.8
0°-90°	346.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	346.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1971	
5°	1771	140
15°	490	138
25°	90	45
35°	23	15
45°	6	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P738963

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1970.7
0.5°	1970.7
1°	1968.3
1.5°	1963.4
2°	1954.4
2.5°	1942.5
3°	1925.6
3.5°	1902.1
4°	1867.2
4.5°	1824.7
5°	1771.2
5.5°	1700.8
6°	1628.7
6.5°	1546.1
7°	1465.2
7.5°	1370.4
8°	1285.8
8.5°	1200.7
9°	1122.1
9.5°	1049.9
10°	982.7
12.5°	705.6
15°	490.0
17.5°	320.1
20°	201.8
22.5°	130.7
25°	89.9
27.5°	63.2
30°	45.5
32.5°	32.6
35°	23.2
37.5°	16.1
40°	11.6
42.5°	8.4
45°	6.3
47.5°	4.9
50°	3.3
52.5°	2.1
55°	1.6
57.5°	1.2
60°	0.9
62.5°	0.7
65°	0.5



TEST NUMBER: P738963

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBSQW1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	0.4
70°	0.2



(END OF REPORT)