

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747343

Luminaire Tested: LD4D35BD010-EU4DR6520359040-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P747343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6520359040-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2974.5 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747343

CATALOG NUMBER: LD4D35BD010-EU4DR6520359040-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P747343

CATALOG NUMBER: LD4D35BD010-EU4DR6520359040-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157737
5°	157337
10°	157205
15°	152358
20°	138705
25°	120873
30°	100531
35°	79654
40°	57493
45°	36317
50°	18935
55°	10060
60°	5280
65°	2902
70°	1212
75°	1354
80°	942
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36317 cd/sqm



TEST NUMBER: P747343

CATALOG NUMBER: LD4D35BD010-EU4DR6520359040-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.4	8.6
10°-20°	699.4	23.5
20°-30°	854.9	28.7
30°-40°	693.7	23.3
40°-50°	345.7	11.6
50°-60°	96.4	3.2
60°-70°	21.9	0.7
70°-80°	5.7	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1809.7	60.8
0°-40°	2503.4	84.2
0°-60°	2945.5	99.0
0°-90°	2974.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2974.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2701	
5°	2684	255
15°	2520	699
25°	1876	855
35°	1117	694
45°	440	346
55°	99	96
65°	21	22
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P747343

CATALOG NUMBER: LD4D35BD010-EU4DR6520359040-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2700.8
2.5°	2698.8
5°	2683.7
7.5°	2675.0
10°	2650.8
12.5°	2601.6
15°	2519.8
17.5°	2392.0
20°	2231.7
22.5°	2058.6
25°	1875.7
27.5°	1680.0
30°	1490.7
32.5°	1303.8
35°	1117.2
37.5°	931.1
40°	754.1
42.5°	588.2
45°	439.7
47.5°	306.4
50°	208.4
52.5°	143.7
55°	98.8
57.5°	66.7
60°	45.2
62.5°	31.4
65°	21.0
67.5°	10.7
70°	7.1
72.5°	6.7
75°	6.0
77.5°	4.0
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)