

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756083

Luminaire Tested: LD4D95BD010-EU4DR2570959040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR2570959040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8320.5 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756083

CATALOG NUMBER: LD4D95BD010-EU4DR2570959040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P756083

CATALOG NUMBER: LD4D95BD010-EU4DR2570959040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3448040
5°	3211419
10°	2290785
15°	1349191
20°	839478
25°	460704
30°	210693
35°	79790
40°	36142
45°	21725
50°	9026
55°	5810
60°	4065
65°	2740
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21725 cd/sqm



TEST NUMBER: P756083

CATALOG NUMBER: LD4D95BD010-EU4DR2570959040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2516.4	30.2
10°-20°	3408.3	41.0
20°-30°	1803.6	21.7
30°-40°	445.2	5.4
40°-50°	108.6	1.3
50°-60°	28.6	0.3
60°-70°	9.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7728.3	92.9
0°-40°	8173.5	98.2
0°-60°	8310.8	99.9
0°-90°	8320.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8320.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31558	
5°	29280	###
15°	11928	3408
25°	3822	1804
35°	598	445
45°	141	109
55°	30	29
65°	11	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756083

CATALOG NUMBER: LD4D95BD010-EU4DR2570959040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	31557.9
2.5°	31039.2
5°	29280.4
7.5°	25746.7
10°	20647.7
12.5°	15608.5
15°	11927.6
17.5°	9295.9
20°	7219.9
22.5°	5414.6
25°	3821.5
27.5°	2562.7
30°	1670.0
32.5°	1016.1
35°	598.2
37.5°	366.1
40°	253.4
42.5°	193.7
45°	140.6
47.5°	84.9
50°	53.1
52.5°	38.5
55°	30.5
57.5°	23.9
60°	18.6
62.5°	14.6
65°	10.6
67.5°	4.0
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)