

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756160

Luminaire Tested: LD4D95BD010-EU4DR3070959040-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3070959040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7321.2 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756160

CATALOG NUMBER: LD4D95BD010-EU4DR3070959040-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P756160

CATALOG NUMBER: LD4D95BD010-EU4DR3070959040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1801931	1801931	1801931
5°	1750204	1748160	1750288
10°	1515941	1505246	1515583
15°	989078	983761	978816
20°	491822	510272	491162
25°	247744	279373	242668
30°	99194	108077	86423
35°	46011	44067	36938
40°	19864	22062	18705
45°	14007	17396	14137
50°	4823	12658	5097
55°	2776	5245	2936
60°	1944	2296	1944
65°	1250	1250	1250
70°	783	515	783
75°	0	355	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 17396 cd/sqm



TEST NUMBER: P756160

CATALOG NUMBER: LD4D95BD010-EU4DR3070959040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2070.1	28.3
10°-20°	3333.9	45.5
20°-30°	1440.7	19.7
30°-40°	328.4	4.5
40°-50°	112.7	1.5
50°-60°	27.5	0.4
60°-70°	7.1	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6844.7	93.5
0°-40°	7173.1	98.0
0°-60°	7313.3	99.9
0°-90°	7321.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7321.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	23541	23541	23541	23541	23541	
5°	22778	22756	22752	22799	22780	2072
15°	12482	12331	12414	12374	12352	3342
25°	2933	3044	3308	2967	2873	1404
35°	492	503	472	468	395	334
45°	129	161	161	161	131	92
55°	21	22	39	23	22	20
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P756160

CATALOG NUMBER: LD4D95BD010-EU4DR3070959040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	23541.3	23541.3	23541.3	23541.3	23541.3
2.5°	23385.2	23369.1	23378.3	23389.9	23394.5
5°	22778.5	22756.5	22751.9	22799.3	22779.6
7.5°	21554.5	21523.3	21475.9	21583.4	21683.9
10°	19504.1	19469.4	19366.5	19417.4	19499.5
12.5°	16477.0	16364.9	16362.6	16524.4	16502.5
15°	12481.5	12331.2	12414.4	12374.0	12352.0
17.5°	8393.4	8335.6	8446.6	8413.0	8268.6
20°	6037.9	6052.9	6264.4	6158.1	6029.8
22.5°	4405.9	4460.2	4711.0	4437.1	4336.6
25°	2933.4	3044.4	3307.9	2966.9	2873.3
27.5°	1804.2	1855.1	2122.0	1781.1	1730.2
30°	1122.3	1096.9	1222.8	1049.5	977.8
32.5°	736.2	703.9	744.3	668.1	610.3
35°	492.4	502.8	471.6	468.1	395.3
37.5°	307.4	353.7	312.1	332.9	254.3
40°	198.8	256.6	220.8	243.9	187.2
42.5°	163.0	197.6	181.5	193.0	166.4
45°	129.4	160.7	160.7	160.7	130.6
47.5°	71.7	107.5	137.5	109.8	76.3
50°	40.5	54.3	106.3	56.6	42.8
52.5°	27.7	31.2	72.8	32.4	28.9
55°	20.8	22.0	39.3	23.1	22.0
57.5°	16.2	17.3	20.8	17.3	16.2
60°	12.7	12.7	15.0	13.9	12.7
62.5°	9.2	9.2	10.4	9.2	9.2
65°	6.9	6.9	6.9	6.9	6.9
67.5°	3.5	4.6	4.6	4.6	4.6
70°	3.5	2.3	2.3	2.3	3.5
72.5°	2.3	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)