

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748303

Luminaire Tested: LD4D45BD010-EU4DR2540509050-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P748303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR2540509050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2964.6 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748303

CATALOG NUMBER: LD4D45BD010-EU4DR2540509050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748303

CATALOG NUMBER: LD4D45BD010-EU4DR2540509050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	90	90	89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	87	87	85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	83	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	80	80	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	78	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	75	75	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	73	73	72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	70	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1228539
5°	1144228
10°	816210
15°	480716
20°	299112
25°	164149
30°	75067
35°	28437
40°	12879
45°	7741
50°	3213
55°	2076
60°	1442
65°	982
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7741 cd/sqm



TEST NUMBER: P748303

CATALOG NUMBER: LD4D45BD010-EU4DR2540509050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	896.6	30.2
10°-20°	1214.4	41.0
20°-30°	642.6	21.7
30°-40°	158.6	5.4
40°-50°	38.7	1.3
50°-60°	10.2	0.3
60°-70°	3.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2753.6	92.9
0°-40°	2912.2	98.2
0°-60°	2961.1	99.9
0°-90°	2964.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2964.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11244	
5°	10433	897
15°	4250	1214
25°	1362	643
35°	213	159
45°	50	39
55°	11	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748303

CATALOG NUMBER: LD4D45BD010-EU4DR2540509050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	11244.1
2.5°	11059.3
5°	10432.6
7.5°	9173.6
10°	7356.8
12.5°	5561.3
15°	4249.8
17.5°	3312.1
20°	2572.5
22.5°	1929.2
25°	1361.6
27.5°	913.1
30°	595.0
32.5°	362.0
35°	213.2
37.5°	130.4
40°	90.3
42.5°	69.0
45°	50.1
47.5°	30.2
50°	18.9
52.5°	13.7
55°	10.9
57.5°	8.5
60°	6.6
62.5°	5.2
65°	3.8
67.5°	1.4
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)