

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756238

Luminaire Tested: LD4D95BD010-EU4DR3570959040-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7699.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756238

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P756238

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2314547
5°	2260159
10°	2037007
15°	1581043
20°	896743
25°	348877
30°	130150
35°	71346
40°	46626
45°	28385
50°	18069
55°	12763
60°	9331
65°	5067
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28385 cd/sqm

TEST NUMBER: P756238

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1895.3	24.6
10°-20°	3700.4	48.1
20°-30°	1509.1	19.6
30°-40°	361.1	4.7
40°-50°	150.5	2.0
50°-60°	62.3	0.8
60°-70°	19.5	0.3
70°-80°	0.5	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7104.8	92.3
0°-40°	7465.9	97.0
0°-60°	7678.7	99.7
0°-90°	7699.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7699.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21184	
5°	20607	###
15°	13977	3700
25°	2894	1509
35°	535	361
45°	184	151
55°	67	62
65°	20	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756238

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	21183.7
2.5°	21056.6
5°	20607.2
7.5°	19710.7
10°	18360.3
12.5°	16458.7
15°	13977.3
17.5°	10942.5
20°	7712.4
22.5°	4917.9
25°	2893.9
27.5°	1635.8
30°	1031.6
32.5°	724.3
35°	534.9
37.5°	413.6
40°	326.9
42.5°	251.8
45°	183.7
47.5°	137.5
50°	106.3
52.5°	84.3
55°	67.0
57.5°	54.3
60°	42.7
62.5°	31.2
65°	19.6
67.5°	6.9
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)