

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756243

Luminaire Tested: LD4D95BD010-EU4DR3570959040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9362.8 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756243

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P756243

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2814721
5°	2748588
10°	2477208
15°	1922707
20°	1090535
25°	424272
30°	158285
35°	86765
40°	56710
45°	34519
50°	21978
55°	15525
60°	11363
65°	6179
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34519 cd/sqm

TEST NUMBER: P756243

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2304.8	24.6
10°-20°	4500.0	48.1
20°-30°	1835.3	19.6
30°-40°	439.2	4.7
40°-50°	183.1	2.0
50°-60°	75.8	0.8
60°-70°	23.7	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8640.1	92.3
0°-40°	9079.3	97.0
0°-60°	9338.2	99.7
0°-90°	9362.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9362.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25762	
5°	25060	###
15°	16998	4500
25°	3519	1835
35°	650	439
45°	223	183
55°	82	76
65°	24	24
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P756243

CATALOG NUMBER: LD4D95BD010-EU4DR3570959040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	25761.5
2.5°	25607.0
5°	25060.5
7.5°	23970.3
10°	22328.0
12.5°	20015.5
15°	16997.8
17.5°	13307.1
20°	9379.1
22.5°	5980.6
25°	3519.3
27.5°	1989.3
30°	1254.6
32.5°	880.9
35°	650.5
37.5°	503.0
40°	397.6
42.5°	306.3
45°	223.4
47.5°	167.2
50°	129.3
52.5°	102.6
55°	81.5
57.5°	66.0
60°	52.0
62.5°	37.9
65°	23.9
67.5°	8.4
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)