

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749200

Luminaire Tested: LD4D50D010-EU4DR3540509030-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR3540509030-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3961.1 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749200

CATALOG NUMBER: LD4D50D010-EU4DR3540509030-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P749200

CATALOG NUMBER: LD4D50D010-EU4DR3540509030-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1190800
5°	1162829
10°	1048010
15°	813422
20°	461359
25°	179496
30°	66968
35°	36707
40°	23990
45°	14602
50°	9298
55°	6572
60°	4807
65°	2611
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14602 cd/sqm



TEST NUMBER: P749200

CATALOG NUMBER: LD4D50D010-EU4DR3540509030-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	975.1	24.6
10°-20°	1903.8	48.1
20°-30°	776.4	19.6
30°-40°	185.8	4.7
40°-50°	77.4	2.0
50°-60°	32.1	0.8
60°-70°	10.0	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3655.3	92.3
0°-40°	3841.1	97.0
0°-60°	3950.6	99.7
0°-90°	3961.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3961.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10899	
5°	10602	975
15°	7191	1904
25°	1489	776
35°	275	186
45°	94	77
55°	34	32
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P749200

CATALOG NUMBER: LD4D50D010-EU4DR3540509030-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10898.7
2.5°	10833.4
5°	10602.2
7.5°	10140.9
10°	9446.1
12.5°	8467.8
15°	7191.1
17.5°	5629.8
20°	3967.9
22.5°	2530.2
25°	1488.9
27.5°	841.6
30°	530.8
32.5°	372.7
35°	275.2
37.5°	212.8
40°	168.2
42.5°	129.6
45°	94.5
47.5°	70.7
50°	54.7
52.5°	43.4
55°	34.5
57.5°	27.9
60°	22.0
62.5°	16.0
65°	10.1
67.5°	3.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)