

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756551

Luminaire Tested: LD4D95BD010-EU4DR5570959040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9522.3 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756551

CATALOG NUMBER: LD4D95BD010-EU4DR5570959040-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P756551

CATALOG NUMBER: LD4D95BD010-EU4DR5570959040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1166664
5°	1120329
10°	1116097
15°	1084038
20°	971995
25°	803300
30°	606796
35°	439976
40°	281565
45°	128605
50°	42053
55°	18154
60°	7801
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 128605 cd/sqm



TEST NUMBER: P756551

CATALOG NUMBER: LD4D95BD010-EU4DR5570959040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	972.0	10.2
10°-20°	2652.7	27.9
20°-30°	3023.0	31.7
30°-40°	2057.9	21.6
40°-50°	709.1	7.4
50°-60°	98.0	1.0
60°-70°	9.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6647.7	69.8
0°-40°	8705.6	91.4
0°-60°	9512.8	99.9
0°-90°	9522.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9522.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10678	
5°	10215	972
15°	9584	2653
25°	6663	3023
35°	3299	2058
45°	832	709
55°	95	98
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756551

CATALOG NUMBER: LD4D95BD010-EU4DR5570959040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	10677.8
2.5°	10433.0
5°	10214.7
7.5°	10107.5
10°	10059.8
12.5°	9901.1
15°	9583.5
17.5°	9079.4
20°	8359.6
22.5°	7528.7
25°	6663.3
27.5°	5762.3
30°	4809.6
32.5°	4002.5
35°	3298.6
37.5°	2629.1
40°	1974.1
42.5°	1368.1
45°	832.3
47.5°	448.5
50°	247.4
52.5°	146.9
55°	95.3
57.5°	60.9
60°	35.7
62.5°	15.9
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)