

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740928

Luminaire Tested: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 645.9 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740928

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P740928

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401675
5°	362387
10°	203387
15°	103387
20°	43777
25°	20205
30°	10699
35°	5762
40°	3081
45°	1823
50°	1054
55°	552
60°	350
65°	259
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1823 cd/sqm



TEST NUMBER: P740928

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.7	40.5
10°-20°	257.7	39.9
20°-30°	84.2	13.0
30°-40°	28.7	4.4
40°-50°	9.6	1.5
50°-60°	2.9	0.4
60°-70°	1.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.7	93.5
0°-40°	632.3	97.9
0°-60°	644.9	99.8
0°-90°	645.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3676	
5°	3304	262
15°	914	258
25°	168	84
35°	43	29
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740928

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3676.3
0.5°	3676.3
1°	3671.7
1.5°	3662.5
2°	3645.8
2.5°	3623.6
3°	3592.1
3.5°	3548.3
4°	3483.1
4.5°	3403.9
5°	3304.1
5.5°	3172.8
6°	3038.2
6.5°	2884.0
7°	2733.1
7.5°	2556.4
8°	2398.6
8.5°	2239.8
9°	2093.1
9.5°	1958.6
10°	1833.2
12.5°	1316.3
15°	914.0
17.5°	597.1
20°	376.5
22.5°	243.9
25°	167.6
27.5°	117.8
30°	84.8
32.5°	60.9
35°	43.2
37.5°	30.1
40°	21.6
42.5°	15.7
45°	11.8
47.5°	9.2
50°	6.2
52.5°	3.9
55°	2.9
57.5°	2.3
60°	1.6
62.5°	1.3
65°	1.0



TEST NUMBER: P740928

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9024-4LBCSSQMMS

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	0.7
70°	0.3



(END OF REPORT)