

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756408

Luminaire Tested: LD4D95BD010-EU4DR4570959050-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756408  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR4570959050-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9605.7 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P756408

CATALOG NUMBER: LD4D95BD010-EU4DR4570959050-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P756408

CATALOG NUMBER: LD4D95BD010-EU4DR4570959050-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 98  |
| 2   | 109 | 105 | 102 | 99  | 107 | 103 | 100 | 98  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 91  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 79  |  | 83  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  |
| 7   | 89  | 81  | 75  | 72  | 87  | 80  | 75  | 72  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  |
| 8   | 85  | 77  | 72  | 68  | 84  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 9   | 82  | 73  | 68  | 65  | 81  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 67  | 64  |  | 71  |
| 10  | 79  | 70  | 65  | 62  | 78  | 70  | 65  | 62  | 69  | 65  | 62  |  | 68  | 64  | 61  |  | 68  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1855062 |
| 5°  | 1802253 |
| 10° | 1724260 |
| 15° | 1578068 |
| 20° | 1251956 |
| 25° | 781612  |
| 30° | 430798  |
| 35° | 193432  |
| 40° | 76193   |
| 45° | 35910   |
| 50° | 17032   |
| 55° | 8896    |
| 60° | 4370    |
| 65° | 1034    |
| 70° | 415     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35910 cd/sqm



TEST NUMBER: P756408

CATALOG NUMBER: LD4D95BD010-EU4DR4570959050-4LBDP1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1544.0 | 16.1      |
| 10°-20°   | 3799.9 | 39.6      |
| 20°-30°   | 3009.1 | 31.3      |
| 30°-40°   | 1002.1 | 10.4      |
| 40°-50°   | 198.9  | 2.1       |
| 50°-60°   | 45.2   | 0.5       |
| 60°-70°   | 6.5    | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 8352.9 | 87.0      |
| 0°-40°    | 9355.0 | 97.4      |
| 0°-60°    | 9599.1 | 99.9      |
| 0°-90°    | 9605.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 9605.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 16978 |      |
| 5°  | 16432 | ###  |
| 15° | 13951 | 3800 |
| 25° | 6483  | 3009 |
| 35° | 1450  | 1002 |
| 45° | 232   | 199  |
| 55° | 47    | 45   |
| 65° | 4     | 6    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P756408

CATALOG NUMBER: LD4D95BD010-EU4DR4570959050-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 16978.3 |
| 2.5°  | 16867.5 |
| 5°    | 16432.2 |
| 7.5°  | 16072.9 |
| 10°   | 15541.4 |
| 12.5° | 14833.7 |
| 15°   | 13951.0 |
| 17.5° | 12623.6 |
| 20°   | 10767.4 |
| 22.5° | 8555.9  |
| 25°   | 6483.4  |
| 27.5° | 4747.4  |
| 30°   | 3414.6  |
| 32.5° | 2322.3  |
| 35°   | 1450.2  |
| 37.5° | 860.0   |
| 40°   | 534.2   |
| 42.5° | 351.2   |
| 45°   | 232.4   |
| 47.5° | 149.6   |
| 50°   | 100.2   |
| 52.5° | 66.8    |
| 55°   | 46.7    |
| 57.5° | 30.7    |
| 60°   | 20.0    |
| 62.5° | 10.7    |
| 65°   | 4.0     |
| 67.5° | 1.3     |
| 70°   | 1.3     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report







(END OF REPORT)