

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205587

Luminaire Tested: **LD4B15D010 EU4B10208027 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208027 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1424.5 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205587

CATALOG NUMBER: LD4B15D010 EU4B10208027 4LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P205587

CATALOG NUMBER: LD4B15D010 EU4B10208027 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	112	108	105	102	109	106	103	101		102	100	97			98	96	94			90
2	104	98	92	88	102	96	91	87		92	88	85			89	86	83			79
3	96	88	82	76	94	87	81	76		84	79	74			81	77	73			70
4	90	80	73	67	88	79	72	67		76	70	66			74	69	65			62
5	83	73	65	59	82	72	64	59		70	63	59			68	62	58			56
6	78	66	59	53	76	65	58	53		64	57	53			62	57	52			50
7	73	61	53	48	71	60	53	48		59	52	48			57	52	47			45
8	68	56	49	44	67	56	48	43		54	48	43			53	47	43			41
9	64	52	45	40	63	52	45	40		50	44	40			49	44	39			38
10	60	48	41	37	59	48	41	37		47	41	36			46	40	36			35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205587

CATALOG NUMBER: LD4B15D010 EU4B10208027 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	5.9
10°-20°	221.1	15.5
20°-30°	297.0	20.8
30°-40°	304.0	21.3
40°-50°	263.1	18.5
50°-60°	175.0	12.3
60°-70°	71.9	5.0
70°-80°	8.6	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.5	42.2
0°-40°	905.5	63.6
0°-60°	1343.6	94.3
0°-90°	1424.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	903	
5°	889	83
15°	790	221
25°	648	297
35°	486	304
45°	343	263
55°	194	175
65°	71	72
75°	4	9
85°	0	0
90°	0	



TEST NUMBER: P205587

CATALOG NUMBER: LD4B15D010 EU4B10208027 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	902.8
2.5°	901.0
5°	888.8
7.5°	870.2
10°	844.9
12.5°	816.9
15°	789.9
17.5°	755.3
20°	721.7
22.5°	686.2
25°	647.9
27.5°	606.9
30°	565.8
32.5°	524.7
35°	485.5
37.5°	448.1
40°	412.7
42.5°	377.2
45°	342.6
47.5°	306.2
50°	268.9
52.5°	231.5
55°	194.2
57.5°	161.5
60°	127.9
62.5°	97.1
65°	71.0
67.5°	46.7
70°	27.1
72.5°	13.1
75°	3.7
77.5°	1.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)