

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756646

Luminaire Tested: LD4D95BD010-EU4DR6070959050-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6070959050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9900.3 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756646

CATALOG NUMBER: LD4D95BD010-EU4DR6070959050-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P756646

CATALOG NUMBER: LD4D95BD010-EU4DR6070959050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1082512
5°	1079869
10°	1115731
15°	1116887
20°	1027654
25°	874091
30°	666029
35°	470988
40°	276573
45°	111593
50°	37260
55°	17925
60°	7364
65°	1086
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 111593 cd/sqm



TEST NUMBER: P756646

CATALOG NUMBER: LD4D95BD010-EU4DR6070959050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	949.8	9.6
10°-20°	2735.4	27.6
20°-30°	3273.9	33.1
30°-40°	2189.7	22.1
40°-50°	649.2	6.6
50°-60°	93.3	0.9
60°-70°	8.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6959.1	70.3
0°-40°	9148.9	92.4
0°-60°	9891.4	99.9
0°-90°	9900.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9900.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9908	
5°	9846	950
15°	9874	2735
25°	7250	3274
35°	3531	2190
45°	722	649
55°	94	93
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756646

CATALOG NUMBER: LD4D95BD010-EU4DR6070959050-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	9907.6
2.5°	9894.9
5°	9845.8
7.5°	9979.3
10°	10056.5
12.5°	10042.5
15°	9873.9
17.5°	9476.2
20°	8838.3
22.5°	8072.5
25°	7250.5
27.5°	6324.5
30°	5279.1
32.5°	4346.1
35°	3531.1
37.5°	2714.7
40°	1939.1
42.5°	1278.7
45°	722.2
47.5°	369.5
50°	219.2
52.5°	141.9
55°	94.1
57.5°	60.4
60°	33.7
62.5°	14.1
65°	4.2
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)