

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756721

Luminaire Tested: LD4D95BD010-EU4DR6570959050-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756721  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR6570959050-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8628.9 lumens  
Efficiency: N/A  
Efficacy: 87.0 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P756721

CATALOG NUMBER: LD4D95BD010-EU4DR6570959050-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P756721

CATALOG NUMBER: LD4D95BD010-EU4DR6570959050-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 74  | 70  | 67  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 73  | 67  | 63  | 71  | 66  | 62  |  | 70  | 66  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 58  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 928258 |
| 5°  | 929028 |
| 10° | 961738 |
| 15° | 963322 |
| 20° | 886906 |
| 25° | 755681 |
| 30° | 578510 |
| 35° | 408698 |
| 40° | 241244 |
| 45° | 97934  |
| 50° | 35509  |
| 55° | 19773  |
| 60° | 11341  |
| 65° | 6231   |
| 70° | 6549   |
| 75° | 5108   |
| 80° | 5348   |
| 85° | 4513   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 97934 cd/sqm



TEST NUMBER: P756721

CATALOG NUMBER: LD4D95BD010-EU4DR6570959050-4LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 818.1  | 9.5       |
| 10°-20°   | 2359.8 | 27.3      |
| 20°-30°   | 2831.3 | 32.8      |
| 30°-40°   | 1902.7 | 22.1      |
| 40°-50°   | 569.6  | 6.6       |
| 50°-60°   | 100.5  | 1.2       |
| 60°-70°   | 28.6   | 0.3       |
| 70°-80°   | 14.0   | 0.2       |
| 80°-90°   | 4.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 6009.1 | 69.6      |
| 0°-40°    | 7911.8 | 91.7      |
| 0°-60°    | 8581.9 | 99.5      |
| 0°-90°    | 8628.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 8628.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8496 |      |
| 5°  | 8470 | 818  |
| 15° | 8516 | 2360 |
| 25° | 6268 | 2831 |
| 35° | 3064 | 1903 |
| 45° | 634  | 570  |
| 55° | 104  | 101  |
| 65° | 24   | 29   |
| 75° | 12   | 14   |
| 85° | 4    | 4    |
| 90° | 0    |      |



TEST NUMBER: P756721

CATALOG NUMBER: LD4D95BD010-EU4DR6570959050-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 8495.8 |
| 2.5°  | 8532.0 |
| 5°    | 8470.5 |
| 7.5°  | 8598.4 |
| 10°   | 8668.5 |
| 12.5° | 8651.6 |
| 15°   | 8516.3 |
| 17.5° | 8185.5 |
| 20°   | 7627.8 |
| 22.5° | 6971.0 |
| 25°   | 6268.3 |
| 27.5° | 5475.1 |
| 30°   | 4585.4 |
| 32.5° | 3778.9 |
| 35°   | 3064.1 |
| 37.5° | 2357.9 |
| 40°   | 1691.4 |
| 42.5° | 1104.7 |
| 45°   | 633.8  |
| 47.5° | 335.6  |
| 50°   | 208.9  |
| 52.5° | 144.9  |
| 55°   | 103.8  |
| 57.5° | 74.9   |
| 60°   | 51.9   |
| 62.5° | 33.8   |
| 65°   | 24.1   |
| 67.5° | 21.7   |
| 70°   | 20.5   |
| 72.5° | 15.7   |
| 75°   | 12.1   |
| 77.5° | 10.9   |
| 80°   | 8.5    |
| 82.5° | 6.0    |
| 85°   | 3.6    |
| 87.5° | 2.4    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)