

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207767

Luminaire Tested: **LD4B15D010 EU4B10209727 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209727 4LBNGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.1 lumens
Efficiency: N/A
Efficacy: 35.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207767

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207767

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207767

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	10.9
10°-20°	136.7	27.3
20°-30°	166.6	33.3
30°-40°	109.9	22.0
40°-50°	25.3	5.1
50°-60°	4.8	1.0
60°-70°	1.8	0.4
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.8	71.5
0°-40°	467.7	93.5
0°-60°	497.9	99.6
0°-90°	500.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	585	55
15°	490	137
25°	366	167
35°	176	110
45°	28	25
55°	5	5
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P207767

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	599.8
2.5°	598.6
5°	585.2
7.5°	567.1
10°	542.8
12.5°	518.6
15°	489.5
17.5°	459.2
20°	427.7
22.5°	399.8
25°	365.9
27.5°	332.0
30°	288.4
32.5°	235.1
35°	175.7
37.5°	122.4
40°	78.8
42.5°	48.5
45°	27.9
47.5°	14.5
50°	8.5
52.5°	7.3
55°	4.8
57.5°	3.6
60°	3.6
62.5°	2.4
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)