

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206943

Luminaire Tested: **LD4B15D010 EU4B10209727 4LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206943
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209727 4LBWB1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 521.9 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206943

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P206943

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105	111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94	105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85	99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77	94	86	81	77		84	79	76		82	78	75		80	77	74
5	90	81	75	70	89	80	74	70		79	73	69		77	72	69		75	71	68
6	85	76	69	65	84	75	69	64		73	68	64		72	67	64		70	66	63
7	80	71	64	60	79	70	64	59		69	63	59		67	62	59		66	62	58
8	76	66	60	55	75	65	59	55		64	59	55		63	58	54		62	58	54
9	72	62	55	51	71	61	55	51		60	55	51		59	54	51		58	54	51
10	68	58	52	48	67	58	52	48		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206943

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	7.9
10°-20°	116.6	22.3
20°-30°	161.1	30.9
30°-40°	137.9	26.4
40°-50°	58.6	11.2
50°-60°	6.5	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	318.8	61.1
0°-40°	456.7	87.5
0°-60°	521.9	100.0
0°-90°	521.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	433	41
15°	414	117
25°	353	161
35°	224	138
45°	74	59
55°	4	7
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P206943

CATALOG NUMBER: LD4B15D010 EU4B10209727 4LBWB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	435.7
2.5°	434.5
5°	433.3
7.5°	430.8
10°	426.0
12.5°	423.6
15°	413.9
17.5°	405.4
20°	392.1
22.5°	376.4
25°	353.4
27.5°	328.0
30°	298.9
32.5°	263.8
35°	223.9
37.5°	182.7
40°	141.6
42.5°	105.3
45°	73.8
47.5°	46.0
50°	26.6
52.5°	13.3
55°	3.6
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)