

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206521

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBSCMMS1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1318.1 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206521

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P206521

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84	99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72	92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62	84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54	78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48	72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42	67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38	63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35	59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31	55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206521

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.0	4.3
10°-20°	160.1	12.1
20°-30°	233.8	17.7
30°-40°	267.4	20.3
40°-50°	257.0	19.5
50°-60°	198.4	15.1
60°-70°	110.8	8.4
70°-80°	32.2	2.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.9	34.2
0°-40°	718.3	54.5
0°-60°	1173.7	89.0
0°-90°	1318.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	605	
5°	600	57
15°	568	160
25°	508	234
35°	428	267
45°	335	257
55°	222	198
65°	111	111
75°	28	32
85°	1	1
90°	0	



TEST NUMBER: P206521

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	605.3
2.5°	605.3
5°	600.2
7.5°	597.6
10°	589.1
12.5°	578.9
15°	567.8
17.5°	556.7
20°	540.5
22.5°	527.7
25°	508.1
27.5°	488.5
30°	468.9
32.5°	449.3
35°	428.0
37.5°	406.7
40°	381.9
42.5°	359.8
45°	335.1
47.5°	306.9
50°	280.5
52.5°	251.5
55°	222.5
57.5°	192.7
60°	164.5
62.5°	136.4
65°	110.8
67.5°	87.0
70°	64.8
72.5°	45.2
75°	28.1
77.5°	14.5
80°	5.1
82.5°	1.7
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)