

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206315

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBSCMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1560.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206315

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206315

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87		
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74		
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63		
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42		
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37		
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33		
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30		
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206315

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	3.9
10°-20°	171.9	11.0
20°-30°	258.5	16.6
30°-40°	306.4	19.6
40°-50°	304.9	19.5
50°-60°	245.8	15.8
60°-70°	148.7	9.5
70°-80°	55.2	3.5
80°-90°	8.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.8	31.5
0°-40°	797.2	51.1
0°-60°	1347.9	86.4
0°-90°	1560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1560.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	637	
5°	634	60
15°	609	172
25°	562	259
35°	491	306
45°	397	305
55°	274	246
65°	149	149
75°	50	55
85°	7	8
90°	0	



TEST NUMBER: P206315

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBSCMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	637.2
2.5°	637.2
5°	634.3
7.5°	632.4
10°	626.8
12.5°	617.3
15°	608.8
17.5°	599.3
20°	588.0
22.5°	576.7
25°	561.5
27.5°	545.5
30°	527.5
32.5°	510.5
35°	490.6
37.5°	469.8
40°	445.3
42.5°	421.6
45°	397.0
47.5°	369.6
50°	339.4
52.5°	308.2
55°	274.1
57.5°	243.9
60°	209.9
62.5°	179.6
65°	149.4
67.5°	121.0
70°	94.5
72.5°	70.9
75°	50.1
77.5°	32.1
80°	18.9
82.5°	11.3
85°	6.6
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)