

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207860

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBNB1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 579.9 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207860

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P207860

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	86	82	97	90	86	82	88	84	81		86	83	80		85
5	94	86	81	77	92	85	80	76	84	79	76		82	78	75		80
6	90	81	76	72	88	81	75	71	79	74	71		78	74	70		76
7	86	77	71	67	84	76	71	67	75	70	67		74	69	66		73
8	82	73	67	63	80	72	67	63	71	66	63		70	66	62		69
9	78	69	63	60	77	68	63	59	67	63	59		67	62	59		66
10	75	65	60	56	74	65	60	56	64	59	56		63	59	56		63

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207860

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	13.6
10°-20°	167.6	28.9
20°-30°	194.5	33.5
30°-40°	121.7	21.0
40°-50°	17.1	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.0	76.1
0°-40°	562.8	97.0
0°-60°	579.9	100.0
0°-90°	579.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	948	
5°	879	79
15°	595	168
25°	429	194
35°	195	122
45°	15	17
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P207860

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	948.3
2.5°	929.6
5°	878.7
7.5°	805.8
10°	731.1
12.5°	659.9
15°	595.4
17.5°	541.2
20°	500.4
22.5°	463.1
25°	429.2
27.5°	388.5
30°	335.9
32.5°	269.7
35°	195.1
37.5°	127.2
40°	72.9
42.5°	37.3
45°	15.3
47.5°	3.4
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)