

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206211

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1594.1 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206211

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P206211

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206211

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	3.8
10°-20°	173.5	10.9
20°-30°	261.3	16.4
30°-40°	310.8	19.5
40°-50°	310.3	19.5
50°-60°	252.3	15.8
60°-70°	155.2	9.7
70°-80°	60.1	3.8
80°-90°	9.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.6	31.1
0°-40°	806.4	50.6
0°-60°	1369.0	85.9
0°-90°	1594.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1594.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	642	
5°	640	61
15°	616	173
25°	569	261
35°	498	311
45°	403	310
55°	282	252
65°	156	155
75°	55	60
85°	8	10
90°	0	



TEST NUMBER: P206211

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	642.2
2.5°	643.2
5°	640.4
7.5°	636.6
10°	631.9
12.5°	623.4
15°	615.8
17.5°	604.5
20°	592.2
22.5°	580.9
25°	568.6
27.5°	551.6
30°	534.6
32.5°	518.5
35°	497.7
37.5°	475.1
40°	454.3
42.5°	428.8
45°	403.3
47.5°	375.9
50°	346.6
52.5°	316.4
55°	282.4
57.5°	249.3
60°	217.2
62.5°	186.1
65°	155.8
67.5°	127.5
70°	101.1
72.5°	76.5
75°	54.8
77.5°	35.9
80°	21.7
82.5°	13.2
85°	7.6
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)