

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746902

Luminaire Tested: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P746902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2695.2 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P746902

CATALOG NUMBER: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS

Luminous Intensity Polar Plot



TEST NUMBER: P746902

CATALOG NUMBER: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	685622
5°	682297
10°	644920
15°	548257
20°	373678
25°	155915
30°	49027
35°	22782
40°	12594
45°	5779
50°	2805
55°	1543
60°	809
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5779 cd/sqm

TEST NUMBER: P746902

CATALOG NUMBER: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	580.9	21.6
10°-20°	1301.3	48.3
20°-30°	651.4	24.2
30°-40°	119.4	4.4
40°-50°	32.9	1.2
50°-60°	7.7	0.3
60°-70°	1.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2533.6	94.0
0°-40°	2653.0	98.4
0°-60°	2693.7	99.9
0°-90°	2695.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2695.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6275	
5°	6221	581
15°	4847	1301
25°	1293	651
35°	171	119
45°	37	33
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746902

CATALOG NUMBER: LD4D35BD010-EU4DR4020359024-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6275.1
2.5°	6266.0
5°	6220.9
7.5°	6077.2
10°	5812.9
12.5°	5400.8
15°	4846.9
17.5°	4126.6
20°	3213.8
22.5°	2191.1
25°	1293.3
27.5°	683.7
30°	388.6
32.5°	251.1
35°	170.8
37.5°	122.1
40°	88.3
42.5°	60.5
45°	37.4
47.5°	23.8
50°	16.5
52.5°	11.7
55°	8.1
57.5°	5.1
60°	3.7
62.5°	2.2
65°	1.1
67.5°	0.7
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)