

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747396

Luminaire Tested: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3172.7 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747396

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P747396

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	273611
5°	272923
10°	272329
15°	272257
20°	269590
25°	253252
30°	225769
35°	180013
40°	119524
45°	71465
50°	37039
55°	19468
60°	6883
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 71465 cd/sqm



TEST NUMBER: P747396

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	7.5
10°-20°	678.7	21.4
20°-30°	957.4	30.2
30°-40°	826.5	26.1
40°-50°	370.1	11.7
50°-60°	96.9	3.1
60°-70°	6.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1872.8	59.0
0°-40°	2699.3	85.1
0°-60°	3166.3	99.8
0°-90°	3172.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3172.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2504	
5°	2488	237
15°	2407	679
25°	2101	957
35°	1350	827
45°	462	370
55°	102	97
65°	0	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747396

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2504.2
2.5°	2501.5
5°	2488.4
7.5°	2477.6
10°	2454.6
12.5°	2433.9
15°	2406.9
17.5°	2375.8
20°	2318.6
22.5°	2224.5
25°	2100.7
27.5°	1957.0
30°	1789.5
32.5°	1584.6
35°	1349.6
37.5°	1090.2
40°	838.0
42.5°	636.7
45°	462.5
47.5°	318.8
50°	217.9
52.5°	150.4
55°	102.2
57.5°	61.7
60°	31.5
62.5°	9.9
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)