

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207036

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1305.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207036

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P207036

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		93
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85
3	96	87	80	75	93	85	79	74	83	77	73		80	76	72		78
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71
5	83	72	64	59	81	71	64	58	69	63	58		67	62	57		65
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	61	49	42	37	59	48	41	37	47	41	37		46	41	37		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207036

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	5.7
10°-20°	207.8	15.9
20°-30°	293.6	22.5
30°-40°	284.4	21.8
40°-50°	191.9	14.7
50°-60°	119.1	9.1
60°-70°	79.6	6.1
70°-80°	43.6	3.3
80°-90°	11.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.6	44.1
0°-40°	860.0	65.9
0°-60°	1171.1	89.7
0°-90°	1305.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1305.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	791	
5°	784	74
15°	737	208
25°	644	294
35°	458	284
45°	246	192
55°	130	119
65°	80	80
75°	41	44
85°	10	12
90°	0	



TEST NUMBER: P207036

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	791.2
2.5°	791.2
5°	784.5
7.5°	776.0
10°	765.8
12.5°	755.7
15°	737.0
17.5°	721.8
20°	696.4
22.5°	670.9
25°	643.8
27.5°	606.6
30°	565.9
32.5°	513.4
35°	457.5
37.5°	401.5
40°	345.6
42.5°	289.7
45°	245.7
47.5°	205.0
50°	174.5
52.5°	149.1
55°	130.5
57.5°	115.2
60°	103.4
62.5°	91.5
65°	79.6
67.5°	69.5
70°	59.3
72.5°	50.8
75°	40.7
77.5°	32.2
80°	23.7
82.5°	16.9
85°	10.2
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)