

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205593

Luminaire Tested: **LD4B15D010 EU4B10209030 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209030 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1271.8 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205593

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205593

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205593

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	5.9
10°-20°	197.4	15.5
20°-30°	265.1	20.8
30°-40°	271.4	21.3
40°-50°	234.9	18.5
50°-60°	156.3	12.3
60°-70°	64.2	5.0
70°-80°	7.6	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.1	42.2
0°-40°	808.5	63.6
0°-60°	1199.7	94.3
0°-90°	1271.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1271.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	806	
5°	794	75
15°	705	197
25°	578	265
35°	434	271
45°	306	235
55°	173	156
65°	63	64
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P205593

CATALOG NUMBER: LD4B15D010 EU4B10209030 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	806.1
2.5°	804.4
5°	793.6
7.5°	776.9
10°	754.4
12.5°	729.4
15°	705.2
17.5°	674.4
20°	644.3
22.5°	612.7
25°	578.5
27.5°	541.8
30°	505.1
32.5°	468.5
35°	433.5
37.5°	400.1
40°	368.4
42.5°	336.8
45°	305.9
47.5°	273.4
50°	240.1
52.5°	206.7
55°	173.4
57.5°	144.2
60°	114.2
62.5°	86.7
65°	63.4
67.5°	41.7
70°	24.2
72.5°	11.7
75°	3.3
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)