

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752714

Luminaire Tested: LD4D70BD010-EU4DR6070959035-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959035-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6743.6 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752714

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P752714

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	737357
5°	735556
10°	759982
15°	760767
20°	699986
25°	595389
30°	453671
35°	320812
40°	188385
45°	76023
50°	25378
55°	12210
60°	5026
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 76023 cd/sqm



TEST NUMBER: P752714

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	646.9	9.6
10°-20°	1863.2	27.6
20°-30°	2230.0	33.1
30°-40°	1491.5	22.1
40°-50°	442.2	6.6
50°-60°	63.6	0.9
60°-70°	6.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4740.2	70.3
0°-40°	6231.7	92.4
0°-60°	6737.6	99.9
0°-90°	6743.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6743.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6749	
5°	6706	647
15°	6726	1863
25°	4939	2230
35°	2405	1492
45°	492	442
55°	64	64
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752714

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6748.6
2.5°	6740.0
5°	6706.5
7.5°	6797.4
10°	6850.0
12.5°	6840.5
15°	6725.6
17.5°	6454.7
20°	6020.2
22.5°	5498.6
25°	4938.7
27.5°	4307.9
30°	3595.9
32.5°	2960.3
35°	2405.2
37.5°	1849.1
40°	1320.8
42.5°	871.0
45°	492.0
47.5°	251.7
50°	149.3
52.5°	96.7
55°	64.1
57.5°	41.2
60°	23.0
62.5°	9.6
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)