

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752648

Luminaire Tested: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7210.9 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P752648

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P752648

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	883472
5°	848393
10°	845189
15°	820910
20°	736065
25°	608325
30°	459513
35°	333177
40°	213217
45°	97377
50°	31854
55°	13734
60°	5922
65°	776
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 97377 cd/sqm



TEST NUMBER: P752648

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	736.1	10.2
10°-20°	2008.8	27.9
20°-30°	2289.2	31.7
30°-40°	1558.4	21.6
40°-50°	537.0	7.4
50°-60°	74.2	1.0
60°-70°	7.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5034.1	69.8
0°-40°	6592.5	91.4
0°-60°	7203.8	99.9
0°-90°	7210.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7210.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8086	
5°	7735	736
15°	7257	2009
25°	5046	2289
35°	2498	1558
45°	630	537
55°	72	74
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752648

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8085.9
2.5°	7900.6
5°	7735.3
7.5°	7654.1
10°	7618.0
12.5°	7497.8
15°	7257.3
17.5°	6875.6
20°	6330.5
22.5°	5701.2
25°	5046.0
27.5°	4363.6
30°	3642.2
32.5°	3031.0
35°	2497.9
37.5°	1990.9
40°	1494.9
42.5°	1036.0
45°	630.2
47.5°	339.7
50°	187.4
52.5°	111.2
55°	72.1
57.5°	46.1
60°	27.1
62.5°	12.0
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)