

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206532

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBSCMMS1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 983.8 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206532

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P206532

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65		
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44		
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40		
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36		
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32		
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206532

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.6	4.3
10°-20°	119.5	12.1
20°-30°	174.5	17.7
30°-40°	199.6	20.3
40°-50°	191.8	19.5
50°-60°	148.1	15.1
60°-70°	82.7	8.4
70°-80°	24.1	2.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.5	34.2
0°-40°	536.1	54.5
0°-60°	876.0	89.0
0°-90°	983.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	983.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	448	43
15°	424	119
25°	379	174
35°	319	200
45°	250	192
55°	166	148
65°	83	83
75°	21	24
85°	1	1
90°	0	



TEST NUMBER: P206532

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	451.8
2.5°	451.8
5°	447.9
7.5°	446.0
10°	439.7
12.5°	432.0
15°	423.8
17.5°	415.5
20°	403.4
22.5°	393.9
25°	379.2
27.5°	364.6
30°	350.0
32.5°	335.3
35°	319.4
37.5°	303.5
40°	285.1
42.5°	268.5
45°	250.1
47.5°	229.1
50°	209.3
52.5°	187.7
55°	166.1
57.5°	143.8
60°	122.8
62.5°	101.8
65°	82.7
67.5°	64.9
70°	48.4
72.5°	33.7
75°	21.0
77.5°	10.8
80°	3.8
82.5°	1.3
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)