

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207974

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207974

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNMW1

Luminous Intensity Polar Plot






TEST NUMBER: P207974

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	105	103		109	106	104	101		102	100	98		98	97	95		95	94	92
2	105	99	94	90		103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	80		96	89	83	79		86	82	78		84	80	76		81	78	75
4	92	83	76	71		90	82	76	71		80	74	70		78	73	69		76	72	68
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	63
6	82	71	64	59		80	70	64	59		69	63	58		67	62	58		66	61	58
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		62	57	53
8	73	62	55	50		71	61	55	50		60	54	50		59	53	49		58	53	49
9	69	58	51	46		68	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	48	43		64	54	47	43		53	47	43		52	47	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207974

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.5	7.8
10°-20°	163.5	20.5
20°-30°	215.1	27.0
30°-40°	167.5	21.0
40°-50°	81.3	10.2
50°-60°	51.4	6.5
60°-70°	33.1	4.2
70°-80°	17.3	2.2
80°-90°	4.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.1	55.4
0°-40°	608.5	76.4
0°-60°	741.3	93.1
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	666	62
15°	583	163
25°	474	215
35°	268	167
45°	101	81
55°	57	51
65°	33	33
75°	16	17
85°	4	4
90°	0	



TEST NUMBER: P207974

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	679.1
2.5°	675.3
5°	666.4
7.5°	651.3
10°	631.0
12.5°	608.3
15°	583.0
17.5°	556.4
20°	528.6
22.5°	502.0
25°	474.2
27.5°	438.8
30°	390.8
32.5°	333.9
35°	268.1
37.5°	207.4
40°	160.6
42.5°	125.2
45°	101.2
47.5°	82.2
50°	72.1
52.5°	64.5
55°	56.9
57.5°	50.6
60°	44.3
62.5°	37.9
65°	32.9
67.5°	29.1
70°	24.0
72.5°	20.2
75°	16.4
77.5°	12.6
80°	8.9
82.5°	6.3
85°	3.8
87.5°	1.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)