

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206738

Luminaire Tested: **LD4B15D010 EU4B10209730 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209730 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 968.2 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206738

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWWH1

Luminous Intensity Polar Plot






TEST NUMBER: P206738

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	64	60		69	64	60		67
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59
9	69	58	51	47	68	58	51	47	57	51	47		56	50	47		55
10	65	54	48	43	64	54	48	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206738

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.7	6.1
10°-20°	181.4	18.7
20°-30°	279.1	28.8
30°-40°	269.3	27.8
40°-50°	140.4	14.5
50°-60°	29.6	3.1
60°-70°	6.9	0.7
70°-80°	2.7	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.2	53.6
0°-40°	788.5	81.4
0°-60°	958.5	99.0
0°-90°	968.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	968.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	605	
5°	610	59
15°	642	181
25°	612	279
35°	437	269
45°	179	140
55°	27	30
65°	6	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P206738

CATALOG NUMBER: LD4B15D010 EU4B10209730 4LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	605.3
2.5°	606.6
5°	610.4
7.5°	615.5
10°	623.1
12.5°	633.2
15°	642.1
17.5°	647.1
20°	643.3
22.5°	635.7
25°	611.7
27.5°	582.5
30°	544.5
32.5°	493.9
35°	436.9
37.5°	374.9
40°	310.3
42.5°	245.7
45°	178.6
47.5°	120.3
50°	77.2
52.5°	46.9
55°	26.6
57.5°	16.5
60°	11.4
62.5°	8.9
65°	6.3
67.5°	5.1
70°	3.8
72.5°	3.8
75°	2.5
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)