

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208484

Luminaire Tested: **LD4B20D010 EU4B10208027 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20D010 EU4B10208027 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1272.5 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208484

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208484

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95						
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89						
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84						
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79						
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75						
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71						
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67						
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64						
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61						
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208484

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	17.4
10°-20°	414.8	32.6
20°-30°	372.2	29.2
30°-40°	213.6	16.8
40°-50°	42.6	3.3
50°-60°	5.4	0.4
60°-70°	2.4	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.2	79.2
0°-40°	1221.7	96.0
0°-60°	1269.7	99.8
0°-90°	1272.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1272.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2704	
5°	2487	221
15°	1489	415
25°	804	372
35°	338	214
45°	46	43
55°	7	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208484

CATALOG NUMBER: LD4B20D010 EU4B10208027 4LBNWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2704.3
2.5°	2649.3
5°	2486.8
7.5°	2249.5
10°	1990.3
12.5°	1735.5
15°	1489.4
17.5°	1274.1
20°	1089.6
22.5°	935.8
25°	804.0
27.5°	698.6
30°	582.2
32.5°	463.5
35°	338.3
37.5°	230.7
40°	142.8
42.5°	85.7
45°	46.1
47.5°	19.8
50°	8.8
52.5°	6.6
55°	6.6
57.5°	4.4
60°	4.4
62.5°	2.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)