

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207551

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1170.1 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207551

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207551

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207551

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.3	7.0
10°-20°	220.7	18.9
20°-30°	293.5	25.1
30°-40°	240.0	20.5
40°-50°	139.8	11.9
50°-60°	92.7	7.9
60°-70°	61.0	5.2
70°-80°	32.2	2.7
80°-90°	7.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.5	51.0
0°-40°	836.6	71.5
0°-60°	1069.1	91.4
0°-90°	1170.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	878	82
15°	786	221
25°	644	293
35°	383	240
45°	176	140
55°	103	93
65°	61	61
75°	30	32
85°	7	8
90°	0	



TEST NUMBER: P207551

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	888.2
2.5°	886.5
5°	878.1
7.5°	857.7
10°	835.7
12.5°	815.3
15°	786.5
17.5°	754.3
20°	727.2
22.5°	689.9
25°	644.1
27.5°	595.0
30°	532.3
32.5°	457.7
35°	383.1
37.5°	315.3
40°	256.0
42.5°	210.2
45°	176.3
47.5°	149.2
50°	130.5
52.5°	115.3
55°	103.4
57.5°	91.5
60°	79.7
62.5°	71.2
65°	61.0
67.5°	52.5
70°	44.1
72.5°	37.3
75°	30.5
77.5°	23.7
80°	17.0
82.5°	11.9
85°	6.8
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)