

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208268

Luminaire Tested: **LD4B15D010 EU4B10208030 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208030 4LBNLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1100.5 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208268

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208268

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99	107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92	103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86	99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80	95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76	91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72	88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68	84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65	81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62	78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208268

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.2	20.3
10°-20°	382.1	34.7
20°-30°	303.7	27.6
30°-40°	160.7	14.6
40°-50°	27.7	2.5
50°-60°	2.1	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.0	82.6
0°-40°	1069.7	97.2
0°-60°	1099.5	99.9
0°-90°	1100.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1100.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2832	
5°	2539	223
15°	1381	382
25°	654	304
35°	254	161
45°	29	28
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208268

CATALOG NUMBER: LD4B15D010 EU4B10208030 4LBNI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2832.2
2.5°	2759.3
5°	2539.0
7.5°	2250.8
10°	1945.7
12.5°	1650.8
15°	1381.3
17.5°	1130.5
20°	930.5
22.5°	778.0
25°	654.2
27.5°	554.2
30°	454.2
32.5°	352.5
35°	254.2
37.5°	167.8
40°	100.0
42.5°	57.6
45°	28.8
47.5°	10.2
50°	3.4
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	1.7
65°	1.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)